


EN4DSC 304 Stainless Steel Disconnect Enclosures - NEMA 4, 4X

ABB Controls, Allen Bradley, Cutler Hammer, General Electric, Siemens I-T-E Max-Flex™, Square D

Disconnect



Cutout Detail



Application

Designed to house the following safety disconnect equipment:

- **ABB Controls** flange mounted variable depth operating mechanisms for disconnect switches and circuit breakers. Cable version for circuit breakers also available.
- **Allen Bradley** 1494V variable depth flange mounted disconnect switches and circuit breaker operators NEMA 4 rated. Will not accept Allen Bradley 1494F disconnect switches, 1494D circuit breaker operators or 1494V-R1, -R2, or -W2 operating handles).
- **Cutler Hammer** C361 variable depth flange mounted disconnect switches and C371 circuit breaker operators. Also Flex-Shaft™ handle mechanisms for circuit breakers. Use Cutler Hammer NEMA 4X rated operating handles to maintain NEMA 4X integrity.
- **Siemens I-T-E Max-Flex™** flange mounted variable depth handles for disconnect switch and circuit breakers. Use handle for NEMA 4 rating.
- **General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers. Also Spec-traFlex™ cable operators for circuit breakers.
- **Square D** Class 9422 disconnect switches with flange mounted variable depth operating mechanisms or cable mechanisms and Class 9422 flange mounted variable depth operating mechanism or cable mechanisms for circuit breakers. SN4SS enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, 9422TG1 or TG2 devices.

Standards

- UL 508 Type 3R, 4 and 4X
- CSA Type 3R, 4 and 4X
- **Complies with**
 - NEMA Type 3R, 4, 4X, 12 and 13
 - JIC EGP-1-1967
 - IEC 60529, IP66
- Appropriate components are required to maintain these standards.

Construction

- Formed 14 or 16 gauge type 304 stainless steel.
- Continuously welded seams.
- Larger sizes include door stiffeners.
- Formed lip on door and enclosure exclude flowing liquids and contaminants.
- Cutouts and holes are provided to suit the flange handle operating mechanism.
- Doors may be easily removed for modifications and are interchangeable.
- Door is secured with easily operated 2 or 3 point handle.
- Cover interlock bracket is welded to the door.
- Collar studs are provided for mounting inner panels.
- Removable inner panel is sold separately.
- Oil resistant gaskets are permanently secured.
- A bonding stud is provided on the door and a grounding stud is provided in the enclosure.
- Includes hardware kit with panel mounting nuts and sealing washers for wall mounting holes.

Note:

- Disconnects and operating mechanisms are not provided with the enclosure, and must be ordered separately from the manufacturer.

Finish

- Door and enclosure are natural, brushed stainless steel.

Accessories

- Additional inner panels...see page [434](#)
- Air conditioners...see page [389](#)
- Blowers...see page [406](#)
- Breather kits...see page [423](#)
- Doorstop kits...see page [447](#)
- Filter fans...see page [408-414](#)
- Heaters...see page [418-420](#)
- Thermostats...see page [421](#)
- Window kits...see page [444](#)


Wallmount Enclosures

EN4DSC 304 Stainless Steel Disconnect Enclosures - NEMA 4, 4X

ABB Controls, Allen Bradley, Cutler Hammer, General Electric, Siemens I-T-E Max-Flex™, Square D

Disconnect

Wallmount Enclosures



CONSULT VARIOUS DISCONNECT MANUFACTURER'S TO OBTAIN L, M, AND P FOR DIFFERENT BRANDS.

K = 4.75 WHEN C = 8.00

K = 11.62 WHEN C = 12.00

P = WIRING BEND SPACE WHEN DISCONNECT IS INSTALLED IN ENCLOSURE

ORDER PANELS SEPERATELY
ALL PANELS ARE 12 GA.

Disconnect Mounting Details

| Part No. | Enclosure Size A x B x C | Door Gauge | Body Gauge | Optional Panel Part No. | Panel Size D x E | Mounting G x H | Latches qty style | # Panel Studs | J |
|----------------|-----------------------------|---------------|---------------|-------------------------------|---------------------|-------------------|----------------------|------------------|-------|
| EN4DSC20228SS | 20.00 x 22.00 x 8.00 | 14 | 16 | EP2020 | 18.17 x 18.17 | 18.50 x 20.50 | 1 2-pt | 4 | 5.00 |
| EN4DSC24228SS | 24.00 x 22.00 x 8.00 | 14 | 16 | EP2420 | 22.17 x 18.17 | 22.50 x 20.50 | 1 2-pt | 4 | 6.00 |
| EN4DSC24268SS | 24.00 x 26.00 x 8.00 | 14 | 16 | EP2424 | 22.17 x 22.17 | 22.50 x 24.50 | 1 2-pt | 4 | 6.00 |
| EN4DSC30268SS | 30.00 x 26.00 x 8.00 | 14 | 16 | EP3024 | 28.17 x 22.17 | 28.50 x 24.50 | 1 2-pt | 4 | 6.00 |
| EN4DSC36268SS | 36.00 x 26.00 x 8.00 | 14 | 16 | EP3624 | 34.17 x 22.17 | 34.50 x 24.50 | 1 2-pt | 6 | 6.00 |
| EN4DSC36328SS | 36.00 x 32.00 x 8.00 | 14 | 14 | EP3630 | 34.17 x 28.17 | 34.50 x 30.50 | 1 2-pt | 6 | 6.00 |
| EN4DSC423212SS | 42.00 x 32.00 x 12.00 | 14 | 14 | EP4230 | 40.17 x 28.17 | 40.50 x 30.50 | 1 3-pt | 6 | 21.00 |
| EN4DSC423812SS | 42.00 x 38.00 x 12.00 | 14 | 14 | EP4236 | 40.17 x 34.17 | 40.50 x 36.50 | 1 3-pt | 8 | 21.00 |
| EN4DSC483812SS | 48.00 x 38.00 x 12.00 | 14 | 14 | EP4836 | 46.17 x 34.17 | 46.50 x 36.50 | 1 3-pt | 8 | 24.00 |
| EN4DSC603812SS | 60.00 x 38.00 x 12.00 | 14 | 14 | EP6036 | 58.17 x 34.17 | 58.50 x 36.50 | 1 3-pt | 8 | 30.00 |

Technical references and DXF downloads available at www.hammondenclosuresales.com

All dimensions in inches unless specified otherwise

Quality Enclosures. Service Excellence.

Gross Automation (877) 268-3700 · www.hammondenclosuresales.com · sales@grossautomation.com